



**TYPE 8483 MOLESOURCE™ KIT**

8481 200W MoleSource  
 82833 200W Electronic Ballast  
 58119 Moleded Case  
 MSR200HR 200 Watt Globe  
**SIZE:** 15" x 20 1/2" x 9 1/2"  
**WEIGHT:** 13 lbs.

*Optional Accessory:*

82852 Head Extension Cable—15 ft.  
 84830 MoleSource Adapter

**TYPE 8481 200 WATT MOLESOURCE™**  
 Using 200 Watt, MSR200HR 5600°K HMI Lamp.

Distance Feet	Light Intensity F.C.	Field Diameter FT.
<b>19° 200W</b>		
30	530	9.0
50	190	15.0
<b>26° 200W</b>		
20	830	8.8
40	208	17.6
<b>36° 200W</b>		
10	1840	6.1
30	204	18.3
<b>50° 200W</b>		
10	1200	9.0
30	133	27.0



**TYPE 84921 MOLESOURCE™ KIT**

8491 400W MoleSource  
 82926 400W Electronic Ballast  
 58119 Moleded Case  
 MSR400HR 400 Watt Globe  
**SIZE:** 15" x 20 1/2" x 9 1/2"  
**WEIGHT:** 16 lbs

*Optional Accessory:*

82956 Head Extension Cable—15 ft  
 84830 MoleSource Adapter

**TYPE 8491 400 WATT MOLESOURCE™**  
 Using 400 Watt, MSR400HR 5600°K HMI Lamp.

Distance Feet	Light Intensity F.C.	Field Diameter FT.
<b>19° 400W</b>		
30	711	9.0
50	256	15.0
<b>26° 400W</b>		
20	990	8.8
40	248	17.6
<b>36° 400W</b>		
10	2000	6.1
30	278	18.3
<b>50° 400W</b>		
10	1280	9.0
30	142	27.0



**TYPE 8484 MOLESOURCE™ KIT**

8481 200W MoleSource  
 82833 200W Electronic Ballast  
 58120 Moleded Case  
 MSR200HR 200 Watt Globe  
 84840 Clear Glass  
 84841 Frosted Glass  
 FVWD2M Lightbank Whitedome Medium  
 82852 Head Extension Cable—15 ft  
 84830 MoleSource Adapter  
**SIZE:** 32" x 14" x 9 1/4"  
**WEIGHT:** 23

**TYPE 8481 200 WATT MOLESOURCE™**  
 Using 200 Watt, MSR200HR 5600°K HMI Lamp.

Distance Feet	Photo Flex Small		Photo Flex Medium	
	Light Intensity F.C.	Beam Dia. Feet	Light Intensity F.C.	Beam Dia. Feet
5	51	8	28	8
8	20	13	11	13
10	13	16	7	16
12	9	19	5	19

\*Light tapers smoothly at edge of field. Diameter listed are flat area diameters at which the intensities are approximately 50% of tabulated intensities at beam center.



**TYPE 84927 MOLESOURCE™ KIT**

8491 400W MoleSource  
 82926 400W Electronic Ballast  
 58120 Moleded Case  
 MSR400HR 400 Watt Globe  
 84840 Clear Glass  
 84841 Frosted Glass  
 FVWD2M Lightbank Whitedome Medium  
 82956 Head Extension Cable—15 ft  
 84830 MoleSource Adapter  
**SIZE:** 32" x 14" x 9 1/4"  
**WEIGHT:** 26

**TYPE 8491 400 WATT MOLESOURCE™**  
 Using 400 Watt, MSR400HR 5600°K HMI Lamp.

Distance Feet	Photo Flex Small		Photo Flex Medium	
	Light Intensity F.C.	Beam Dia. Feet	Light Intensity F.C.	Beam Dia. Feet
5	93	8	51	8
8	36	13	20	13
10	23	16	13	16
12	16	19	9	19

\*Light tapers smoothly at edge of field. Diameter listed are flat area diameters at which the intensities are approximately 50% of tabulated intensities at beam center.

# MoleSource™



937 N. Sycamore Avenue, Hollywood, California, 90038-2384

Tel: (323) 851-0111 • Fax: (323) 851-5593

E-Mail: info@mole.com • Web: www.mole.com



© 2008 Mole-Richardson Company



Mole-Richardson Co.

# MoleSource™

The MoleSource™ offers a Daylight option to the Source Four™ fixture from ETC. These units are available in 200W and 400W models with a 3-point socket adjustment system. With the Source Four's™ wide range of lens options and third party accessories, the MoleSource™ compliments this system by replacing the lamp socket assembly with a bright, HMI daylight source. Light output more than doubles with the addition of the MoleSource™ fixture. No modification are required to the Source Four™ and it remains compatible with all accessories. The MoleSource™ is compatible with Standard or Zoom units and due to its compact design, does not limit the operating position of the Source Four™.



Insert either the  
**MSR200HR** 200W globe  
or the  
**MSR400HR** 400W globe

Start with the  
**Type 8481** 200W MoleSource™  
or the  
**Type 8491** 400W MoleSource™

The MoleSource™ is compatible  
with both the Standard and  
Zoom ETC Source Four™ Fixtures.

## MoleSource™ Lighting System

The MoleSource™ also is very versatile with the use of the MoleSource™ Lightbank Adapter. The adapter mounts on a 5/8" baby pin and allows "bare bulb" style operation that's great for sharp shadow effects. It also provides standard size mounting blocks for many different brand lightbanks and lanterns. Pre-assembled kits include a lightbank from PhotoFlex™ called WhiteDome, which can serve as both directional lightbank or multi directional lantern. The ultra low profile of the MoleSource™ with Lightbank Adapter make it an ideal choice for sets with limited space.



Insert either the  
**MSR200HR** 200W globe  
or the  
**MSR400HR** 400W globe

Start with the  
**Type 8481** 200W MoleSource™  
or the  
**Type 8491** 400W MoleSource™

Attach the  
MoleSource™ to the  
**Type 84830**  
MoleSource™  
Lightbank Adapter.  
Use either the clear  
or frosted beaker.

Together, these units make  
one of the most versatile  
HMI units available today.

Whether the MoleSource™ is used with a lightbank or lantern, or "Bare Bulb", or on a Source 4, our ballasts can provide a convenient and reliable power method. AC ballasts in 200W and 400W models operate at any voltage between 90V and 250V. In 200W models, DC ballasts operate at voltages from 24V to 32V from almost any DC source. New to the family of ballasts is our 200W DC "On-Board" ballasts which accommodate two "Block Style" Anton Bauer 14.4V Hytron 100 Batteries.

## Ballasts



**Type 82833**  
200W AC Ballast



**Type 82926**  
400W AC Ballast



**Type 82850**  
30V DC Ballast



**Type 82865** with On-Board Batteries

